

Technical Data

VLS201612E Type

VLS201612ET-R47N
VLS201612ET-R68N
VLS201612ET-1R0N
VLS201612ET-1R5N
VLS201612ET-2R2M
VLS201612ET-3R3M
VLS201612ET-4R7M
VLS201612ET-6R8M
VLS201612ET-100M


CONTENTS

L-Q Frequency Characteristics
DC Bias & Temperature Characteristics
Temperature Characteristics
Temperature Rise


TDK CORPORATION

L-Q Frequency Characteristics

VLS201612ET-R47N




VLS201612ET-R68N




L-Q Frequency Characteristics

VLS201612ET-1R0N




VLS201612ET-1R5N




L-Q Frequency Characteristics

VLS201612ET-2R2M




VLS201612ET-3R3M




L-Q Frequency Characteristics

VLS201612ET-4R7M




VLS201612ET-6R8M




L-Q Frequency Characteristics

VLS201612ET-100M




DC Bias & Temperature Characteristics (1MHz)

VLS201612ET-R47N




VLS201612ET-R68N




DC Bias & Temperature Characteristics (1MHz)

VLS201612ET-1R0N




VLS201612ET-1R5N




DC Bias & Temperature Characteristics (1MHz)

VLS201612ET-2R2M




VLS201612ET-3R3M




DC Bias & Temperature Characteristics (1MHz)

VLS201612ET-4R7M




VLS201612ET-6R8M




DC Bias & Temperature Characteristics (1MHz)

VLS201612ET-100M




Temperature Rise

VLS201612ET-R47N




VLS201612ET-R68N




Temperature Rise

VLS201612ET-1R0N




VLS201612ET-1R5N




Temperature Rise

VLS201612ET-2R2M




VLS201612ET-3R3M




Temperature Rise

VLS201612ET-4R7M




VLS201612ET-6R8M



Temperature Rise

VLS201612ET-100M



Temperature Characteristic

VLS201612ET

