

Technical Data

VLS201610E Type

VLS201610ET-R47N

VLS201610ET-R68N

VLS201610ET-1R0N

VLS201610ET-1R5N

VLS201610ET-2R2M

VLS201610ET-3R3M

VLS201610ET-4R7M

VLS201610ET-100M

CONTENTS

L-Q Frequency Characteristics

DC Bias & Temperature Characteristics


Temperature Characteristics

Temperature Rise


TDK CORPORATION

L-Q Frequency Characteristics

VLS201610ET-R47N




VLS201610ET-R68N




L-Q Frequency Characteristics

VLS201610ET-1R0N




VLS201610ET-1R5N




L-Q Frequency Characteristics

VLS201610ET-2R2M




VLS201610ET-3R3M




L-Q Frequency Characteristics

VLS201610ET-4R7M




VLS201610ET-6R8M




L-Q Frequency Characteristics

VLS201610ET-100M




DC Bias & Temperature Characteristics (1MHz)

VLS201610ET-R47N




VLS201610ET-R68N




DC Bias & Temperature Characteristics (1MHz)

VLS201610ET-1R0N




VLS201610ET-1R5N




DC Bias & Temperature Characteristics (1MHz)

VLS201610ET-2R2M




VLS201610ET-3R3M




DC Bias & Temperature Characteristics (1MHz)

VLS201610ET-4R7M




VLS201610ET-6R8M




DC Bias & Temperature Characteristics (1MHz)

VLS201610ET-100M




Temperature Rise

VLS201610ET-R47N




VLS201610ET-R68N




Temperature Rise

VLS201610ET-1R0N




VLS201610ET-1R5N




Temperature Rise

VLS201610ET-2R2M




VLS201610ET-3R3M




Temperature Rise

VLS201610ET-4R7M




VLS201610ET-6R8M



Temperature Rise

VLS201610ET-100M



Temperature Characteristic

